

Design Features

- Dry pump cavity
- Self-priming operation
- Runs dry without damage
- Complete isolation of fluid pumped
- Heavy-duty roller bearings
- Variety of pump configurations, flows, and pressure ratings
- No dynamic seals, cups or packing to leak, wear or replace
- Reversible flow
- Low maintenance

Materials of Construction

Non-wetted Parts

Casing: Aluminum Alloy

Rotor: Aluminum Alloy

Rollers: Plastic/Alloy

Wetted Parts


Hose:

EXTRUDED – Hypalon, Varpene, Silicone, PharMed®

BRAIDED – Natural Rubber, EPDM

Inlet/Outlet Connections:

PTFE, Brass or Stainless Steel Hose Barb, Brass NPT, and
Stainless Steel Sanitary Tri-clamp



Dimensional Drawings

Inches (mm)

See Ordering Information for motor
and gearbox sizes

